


New Model Introduction

New model GR-4300-070 is offered as a replacement for model GR-115V. Models have common mounting and tooling and are dimensionally the same except as shown.

Gen 5 Model GR-4300-000

- * 15 to 60mm Diameter
- * 6.4 cm² Piston Area
- * 90° Turn = 0.001mm Adjustment (both axis)
- * +/- 0.200mm Total Adjustment (both axis)



Gen 4 Model GR-115V

- * 15 to 60mm Diameter
- * 6.4 cm² Piston Area
- * X-Axis = 3.1° Turn = 0.001mm Adjustment ▪ ±0.22mm Total Adjustment
- * Y-Axis = 10.4° Turn = 0.001mm Adjustment ▪ ±0.07mm Total Adjustment

